


Serial Number Starting FVV – View 7 Inset (MK1)

stovaxspares.com/appliance/stoves/view-stoves/view-7-insets/view-7-inset-mk1/



- View 7 Inset
- Door Assembly



Read More

| Ref. | Product Code | | Description |
|------|--------------|---|---|
| 1 | MEC8893 |  | View 7 Mk1 Airwash Control Chamber |
| 2 | S7.74 |  | Stockton/View 7 Inset Upper Baffle Plate |
| 3 | S7.70CE |  | Stockton/View 7 Inset Lower Baffle Plate |
| 4 | SM75 |  | Inset Spacer |
| 5 | ME600628 |  | Stockton 7/8 Inset Mk2 Flue Flange |
| 6 | S7.60 |  | Stockton/View 7 Inset Cleanburn Chamber |
| 7 | 4949 |  | 10mm x 2mm Self Adhesive Tape Seal - 2m Pack 1390mm length required. |
| 8 | CE7829 |  | View 7 Side Firebrick Dimensions: 300x205x25mm |
| 9 | MEC8908 |  | View 7 Plinth |
| 10 | RA502571 |  | View 7 Mk1 Secondary Air Control Slider |
| 11 | MEC8820 |  | View 7 Mk1 Ashpan |
| 12 | MEC8900 |  | View 7 Riddling Rod |


| Ref. | Product Code | | Description | |
|------|----------------|---|---|--|
| 13 | MEC8793 |  | Ashpan Tool | |
| 14 | CA7685 |  | Stockton/View 7 Log Guard | |
| 15 | MEC8670 |  | View 7 Mk1 Complete Door Assembly | |
| 16 | MEC8788 |  | Multifunction Tool | |
| 17 | ME600502 |  | View 7 Mk2 Riddling Knob | |
| 18 | S7.61 |  | Stockton/View 7 Inset Main Grate | |
| 19 | CA7663 |  | Stockton 7/8 Inset Mk2 Centre Grate | |
| 20 | ME600599 |  | View/CL3/CL5/CL8 Mk1/CL7 Inset Boiler Door Latch Bolt | |
| 21 | MEC8892 |  | View 7 Top Plate | |
| 22 | N/A Carcass |  | Welded Carcass Assembly | This part is not serviceable and cannot be ordered as a spare. |
| 23 | SS14 |  | Stockton Mk1 3/4/5/6 5in Flue Adapter | |

Drawing: PR9075-4

Do you have the correct appliance?

Before ordering your parts please ensure you have selected the correct appliance. To properly identify your appliance you will need to know your serial number and/or model

number. Please use the following guide to help locate your data badge which contains your serial and model number information.



Read More

| Ref. | Product Code | | Description |
|------|--------------|---|--|
| 1 | CA7646 |  | View 7 Outer Door Frame |
| 2 | ME600422 |  | View Door Spring |
| 3 | MEC9553 |  | View/CL3/CL5/CL8/CL7 Inset Boiler Hinge Assembly |
| 4 | CE7740 |  | View 7 Door Glass Dimensions: 404x368x4mm |
| 5 | 4950 |  | 15mm x 2mm Self Adhesive Tape Seal - 2m Pack 390mm length required |
| 6 | ME600523 |  | View 5/7 Mk1 Primary Air Control Cover Plate |

| Ref. | Product Code | | Description | |
|------|--------------|---|--|---------------------------------------|
| 7 | CA7628 |  | View 3/5/7 Primary Air Control Slider | |
| 8 | CA7647 |  | View 7 Glass Clamp Frame | |
| 9 | N/A |  | Only Used On View 8 Door | This part is not currently available. |
| 10 | 5700 |  | 13mm Black Door Rope Seal with Adhesive - 2m Pack 1700mm+175mm length required. | |
| 11 | 4950 |  | 15mm x 2mm Self Adhesive Tape Seal - 2m Pack 1140mm+400mm length required. | |
| 12 | CA7547 |  | View 3/5/7 Airwash Control Slider | |
| 13 | ME600524 |  | View 5/7 Mk1 Airwash Cover Plate | |
| 14 | FA9510 |  | CL3/CL5/CL8/CL7 Inset Boiler Mk1 Shoulder Screw - Single Screw | |
| 15 | ME600563 |  | View/CL3/CL5/CL8 Large Shoulder Screw | |
| 16 | MEC8641 |  | View Mk1 Door Catch Slider | |

Drawing: PR8903-2

Do you have the correct appliance?

Before ordering your parts please ensure you have selected the correct appliance. To properly identify your appliance you will need to know your serial number and/or model number. Please use the following guide to help locate your data badge which contains your serial and model number information.