


View 5 Wood Burning (MK2)


















stovaxspares.com/appliance/stoves/view-stoves/view-5-stoves/view-5/serial-numbers-starting-cw02000/view-5-wood-mk3/



- View 5 (MK2)
- Door Assembly




Read More

| Ref. | Product Code | | Description | |
|------|--------------|---|---|--|
| 1 | CA7680 |  | Stockton 3/4/5/6/Exmoor/CL3/CL5 Mk2 5" Flue Adapter | |
| 2 | CA7679 |  | Stockton 3/4/5/6/CL3/CL5 Mk2 5" Blanking Plate | |
| 3 | ME500717 |  | Data Plate Mount | |
| 4 | CE7812 |  | View 5/CL5 WB CE Right Hand Side Firebrick Dimensions: 220x315x25mm | |
| 5 | MEC9753 |  | View 5/CL5 Mk2 Secondary Air Slider | |
| 6 | SM32 |  | Stockton/View Mk2 CE Secondary Air Slider Bush | |
| 7 | SM55 |  | Ashpan Tool | |
| 8 | CA7664 |  | View 5/CL5 Log Guard | |
| 9 | MEC8788 |  | Multifunction Tool | |
| 10 | MEC10625 |  | View 5 Complete Door Assembly | |
| 11 | ME600599 |  | View/CL3/CL5/CL8 Mk1/CL7 Inset Boiler Door Latch Bolt | |
| 12 | S5.27 |  | Stockton/View 5 Cleanburn Chamber | |
| 13 | 4949 |  | 10mm x 2mm Self Adhesive Tape Seal - 2m Pack 1155mm length required. | |
| 14 | S5.26 |  | Stockton 5/View 5/CL5 Baffle Plate | |
| 15 | CE7817 |  | View 5/CL5 WB CE Left Hand Side Firebrick Dimensions: 315x220x25mm | |
| 16 | N/A Carcass |  | Welded Carcass Assembly | This part is not serviceable and cannot be ordered as a spare. |
| 17 | MEC8754 |  | View 5 Mk2 Glass Plinth | |

Drawing: PR10522














Do you have the correct appliance?

Before ordering your parts please ensure you have selected the correct appliance. To properly identify your appliance you will need to know your serial number and/or model number. Please use the following guide to help locate your data badge which contains your serial and model number information.



Read MoreRead MoreRead More

| Ref. | Product Code | Description |
|------|--------------|---|
| 1 | CA7596 | View 5 Outer Door Frame |
| 2 | MEC9553 | View/CL3/CL5/CL8/CL7 Inset Boiler Hinge Assembly |
| 3 | CE8098 | View 5 WB Door Glass |
| 4+12 | 4950 | 15mm x 2mm Self Adhesive Tape Seal - 2m Pack 1130mm+340mm length required. |
| 5 | ME601588 | View Mk2 Air Control Handle |
| 6 | ME601583 | View 5/7 Mk2 Primary Air Control Cover Plate |

| Ref. | Product Code | | Description | |
|------|--------------|---|--|---------------------------------------|
| 7 | CA7628 |  | View 3/5/7 Primary Air Control Slider | |
| 8 | CA7768 |  | View 5 Woodburning Door Glass Clamp | |
| 9+10 | 5700 |  | 13mm Black Door Rope Seal with Adhesive - 2m Pack 1600mm+175mm length required. | |
| 10 | N/A |  | See part 9 | This part is not currently available. |
| 11 | VW-5SCKIT |  | View 5 MF Mk2 Smoke Control Kit | |
| 12 | N/A |  | See part 4 | This part is not currently available. |
| 13 | CA7547 |  | View 3/5/7 Airwash Control Slider | |
| 14 | ME601582 |  | View 5/7 MF Mk2 Airwash Cover Plate | |
| 15 | MEC10622 |  | View Mk2 Door Catch Slider | |
| 16 | ME600563 |  | View/CL3/CL5/CL8 Large Shoulder Screw | |
| 17 | FA9510 |  | CL3/CL5/CL8/CL7 Inset Boiler Mk1 Shoulder Screw - Single Screw | |
| 18 | ME600422 |  | View Door Spring | |
| 19 | N/A |  | Only used on View 5T | This part is not currently available. |

Drawing: PR10523

Do you have the correct appliance?

Before ordering your parts please ensure you have selected the correct appliance. To properly identify your appliance you will need to know your serial number and/or model number. Please use the following guide to help locate your data badge which contains your serial and model number information.